

TECHNICAL DATA SHEET

Part No. 133-03178
Article No. 133-03178
Type PC5AH6.5



This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.86 "
Height (metric)	21.5 mm
Length (imperial)	0.67 "
Length (metric)	17.0 mm
Max. Bundle Diameter (imperial)	0.19 "
Max. Bundle Diameter (metric)	4.9 mm
Min. Bundle Diameter (imperial)	0.18 "
Min. Bundle Diameter (metric)	4.5 mm
Mounting Hole Diameter (metric)	6.1 - 6.9 mm, 6.35 mm (hexagonal)
Panel Thickness (imperial)	0.05 - 0.06 "
Panel Thickness (metric)	1.2 - 1.6 mm
Width (metric)	10.0 mm

