

TECHNICAL DATA SHEET

Part No. 133-03534
Article No. 133-03534
Type AH6.65MDPLUG



Push pins fasten multiple parts together with a simple press of the thumb.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Blue (BU)
Pkg. Qty.	4500
Carton Qty.	4500
Customs Number	3926909988

Fixation Method	Arrowhead
Length (imperial)	0.81 "
Length (metric)	20.5 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Panel Thickness (imperial)	0.02 - 0.10 "
Panel Thickness (metric)	0.6 - 2.0 mm
Width (imperial)	0.73 "
Width (metric)	18.6 mm