

TECHNICAL DATA SHEET

Part No. 133-03836
Article No. 133-03836
Type SOC23SO18



Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	1500
Carton Qty.	1500
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	1.2 "
Height (metric)	31.2 mm
Length (imperial)	2.04 "
Length (metric)	50.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Offset Length (imperial)	0.889 "
Offset Length (metric)	22.6 mm
Panel Thickness (imperial)	0.02 - 0.19 "
Panel Thickness (metric)	0.6 - 4.7 mm
Tape Bar Length (metric)	50.0 mm
Width (imperial)	1.4 "
Width (metric)	35.56 mm

