

TECHNICAL DATA SHEET

Part No. 133-04043
Article No. 133-04043
Type PC6.5x2FT8.0



This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	1.06 "
Height (metric)	26.9 mm
Length (imperial)	1.17 "
Length (metric)	29.6 mm
Max. Bundle Diameter (imperial)	0.28 "
Max. Bundle Diameter (metric)	7.0 mm
Min. Bundle Diameter (imperial)	0.26 "
Min. Bundle Diameter (metric)	6.5 mm
Mounting Hole Diameter (imperial)	0.31 "
Mounting Hole Diameter (metric)	8.0 mm
Panel Thickness (imperial)	0.02 - 0.20 "
Panel Thickness (metric)	0.6 - 5.5 mm
Width (imperial)	0.39 "
Width (metric)	10.0 mm

RoHS