

# TECHNICAL DATA SHEET

**Part No.** 133-04243  
**Article No.** 133-04243  
**Type** TEC74



HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

|                              |   |
|------------------------------|---|
| <b>Material</b>              | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Metal (MET) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)   |
| <b>UV Resistant</b>          | Yes   |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use  |
| <b>Color</b>                 | Black (BK)  |
| <b>Pkg. Qty.</b>             | 4000  |
| <b>Carton Qty.</b>           | 4000  |
| <b>Customs Number</b>        | 3926909988  |

|                                   |               |
|-----------------------------------|---------------|
| <b>Fixation Method</b>            | Edge Clip     |
| <b>Height (imperial)</b>          | 0.43 "        |
| <b>Height (metric)</b>            | 10.9 mm       |
| <b>Length (imperial)</b>          | 0.56 "        |
| <b>Length (metric)</b>            | 14.3 mm       |
| <b>Offset Length (imperial)</b>   | 0.37 "        |
| <b>Offset Length (metric)</b>     | 9.3 mm        |
| <b>Panel Thickness (imperial)</b> | 0.06 - 0.11 " |
| <b>Panel Thickness (metric)</b>   | 1.4 - 2.8 mm  |
| <b>Tape Bar Length (metric)</b>   | 36.2 mm       |
| <b>Width (imperial)</b>           | 0.63 "        |
| <b>Width (metric)</b>             | 16 mm         |

