

TECHNICAL DATA SHEET

Part No. 133-04486
Article No. 133-04486
Type TEC93



HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS), Metal (MET)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	0.19 "
Height (metric)	4.8 mm
Length (imperial)	0.78 "
Length (metric)	19.7 mm
Offset Length (imperial)	0.26 "
Offset Length (metric)	6.6 mm
Panel Thickness (imperial)	0.11 - 0.12 "
Panel Thickness (metric)	2.8 - 3.1 mm
Tape Bar Length (metric)	36.2 mm
Width (imperial)	0.44 "
Width (metric)	11.1 mm

