

TECHNICAL DATA SHEET

Part No. 133-04509
Article No. 133-04509
Type CCFT6.5LG-TS5



Connector clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, they can be attached to a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Use Conditions	For Indoor Use Only
Color	Light Gray (LTGY)
Pkg. Qty.	4000
Carton Qty.	4000 Bag
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	1.13 "
Length (metric)	28.76 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Panel Thickness (imperial)	0.06 - 0.16 "
Panel Thickness (metric)	1.5 - 4.0 mm
Width (imperial)	0.52 "
Width (metric)	13.2 mm

