

# TECHNICAL DATA SHEET

**Part No.** 133-04724  
**Article No.** 133-04724  
**Type** CCOVAL23OS10



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Operating Temperature, 500h</b>	+329°F (+165°C)
<b>Operating Temperature, 1000h</b>	+320°F (+160°C)
<b>Operating Temperature, 5000h</b>	+257°F (+125°C)
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	1500
<b>Carton Qty.</b>	1500
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree for oval holes
<b>Length (imperial)</b>	1.385 "
<b>Length (metric)</b>	35.2 mm
<b>Mounting Hole Diameter (imperial)</b>	0.24 x 0.48 ", 0.26 x 0.50 ", 0.26 x 0.51 ", 0.28 x 0.47 "
<b>Mounting Hole Diameter (metric)</b>	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
<b>Panel Thickness (imperial)</b>	0.02 - 0.27 "
<b>Panel Thickness (metric)</b>	0.6 - 6.75 mm
<b>Width (imperial)</b>	0.775 "
<b>Width (metric)</b>	19.7 mm

