

TECHNICAL DATA SHEET

Part No. 148-90060
Article No. 148-90060
Type HCRN-3



HelaCon Releasable Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connections and distribution of cable and conductors in electrical installation applications. These connectors have a lever action that opens for insertion and repositioning of wires and snaps closed to establish a secure connection. Suitable for use with solid and stranded wires.

Material	Polycarbonate (PC)
Operating Temperature	-22°F to +185°F (-30°C to +85°C)
Flammability	UL 94 V-0
Halogen Free	Yes
Max Current	32 A
Wire Range (VDE)	0.2 to 4.0 mm ² all types of wire
Stripping Length (imperial)	0.4 "
Stripping Length	10 mm
Use Conditions	For Indoor Use Only
Color	Clear (CL)
Pkg. Qty.	50
Carton Qty.	3150
Customs Number	8536908085

Length (imperial)	0.67 "
Length (metric)	17.0 mm
Max Current	32 A
Max Voltage	450 V
Number of Conductors	3
Stripping Length	10 mm
Stripping Length (imperial)	0.4 "
Width (metric)	20.5 mm

