

TECHNICAL DATA SHEET

Part No. 150-09201
Article No. 150-09201
Type COW20DP7



Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Brown (BN)
Pkg. Qty.	500
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.26 "
Height (metric)	6.6 mm
Length (imperial)	0.8 "
Length (metric)	42.0 mm
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.3 - 7.0 mm
Offset Length (imperial)	0.79 "
Offset Length (metric)	20.0 mm
Panel Thickness (imperial)	0.03 - 0.18 "
Panel Thickness (metric)	0.8 - 4.5 mm
Tape Bar Length (metric)	42.0 mm
Width (imperial)	1.7 "
Width (metric)	42.0 mm

