

TECHNICAL DATA SHEET

Part No. 150-52693
Article No. 150-52693
Type T50SOSFT6SD



Fir tree mounts with ties cables provide a secure grip in mounting holes and protect against dirt and other impurities. The mount provides low insertion and high extraction force, and slides along the cable tie for the proper orientation. This is sold as an assembly with the cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Foot Part Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	6000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.05 "
Height (metric)	1.3 mm
Length (imperial)	6.0 "
Length (metric)	150 mm
Length 2 (imperial)	0.5 "
Length 2 (metric)	11.6 mm
Max. Bundle Diameter (imperial)	1.22 "
Max. Bundle Diameter (metric)	31.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.4 - 7.1 mm
Panel Thickness (imperial)	0.03 - 0.12 "
Panel Thickness (metric)	0.75 - 3.0 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS ✓