

TECHNICAL DATA SHEET

Part No. 150-77950
Article No. 150-77950
Type T30RFT6



HellermannTyton's fir tree mounts provide a secure grip in a mounting hole and protect against dirt and other impurities. The mount can slide along the strap of the cable tie for proper orientation. The fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Foot Part Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.04 "
Height (metric)	1.1 mm
Length (imperial)	6.0 "
Length (metric)	150.0 mm
Length 2 (imperial)	0.46 "
Length 2 (metric)	11.7 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	30.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	135 N
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.4 - 7.1 mm
Panel Thickness (imperial)	0.03 - 0.12 "
Panel Thickness (metric)	0.75 - 3.0 mm
Width (imperial)	0.14 "
Width (metric)	3.5 mm

RoHS✓