

Technical data sheet

Article number:**151-02750****4FAKRACCBOX9X170FT**

| | |
|--------------------------------------|---|
| Material | Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV) |
| Colour | Black (BK) |
| CE Certification | No |
| for Hole Ø (FH) | 9.0 x 17.0 mm |
| Height (H) | 37.8 mm |
| Length (L) | 26.5 mm |
| Operating Temperature | -40 °C to +105 °C |
| Package Content packed in | bag |
| Pack Cont. | 2500 pcs. |
| Panel Thickness | 2.25 mm |
| Panel Thickness max. | 0.6 - 2.25 mm |
| Panel Thickness min. (metric) | 0.6 mm |
| RoHS compliant | Yes |
| Variant | 9.0 x 17.0 mm |
| Width (W) | 18.7 mm |

RoHS 