

TECHNICAL DATA SHEET

Part No. 151-00006
Article No. 151-00006
Type CGS1



This cable guide standoff is designed for the use with HellermannTyton's button head ties. The cable guide standoff stands off bundles from frame rails, providing clearance from bolts and other protrusions for protection against abrasion. This mount also allows the flow-through of salt, dirt and other impurities from the road, preventing unwanted build-up on hoses and harnesses. This product perfectly secures convoluted tubing's up to 26mm in diameter.

Height (imperial)	1.2 "
Height (metric)	30.5 mm
Length (imperial)	2.23 "
Length (metric)	56.6 mm
Width (imperial)	1.0 "
Width (metric)	25.4 mm

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	250
Customs Number	3926909988

