

TECHNICAL DATA SHEET

Part No. 151-00077
Article No. 151-00077
Type CH20D6



Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.3 "
Height (metric)	7.62 mm
Length (imperial)	2.0 "
Length (metric)	50.0 mm
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.4 - 7.0 mm
Offset Length (imperial)	0.79 "
Offset Length (metric)	20.0 mm
Panel Thickness (imperial)	0.02 - 0.06 "
Panel Thickness (metric)	0.6 - 1.4 mm
Tape Bar Length (metric)	50.0 mm

RoHS

