

# TECHNICAL DATA SHEET

**Part No.** HDM190HIRC2  
**Article No.** 151-00134  
**Type** HDM19



These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	100
<b>Carton Qty.</b>	3000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Height (imperial)</b>	0.66 "
<b>Height (metric)</b>	16.7 mm
<b>Length (imperial)</b>	1.43 "
<b>Length (metric)</b>	36.3 mm
<b>Max. Cable Tie Width (imperial)</b>	0.50 "
<b>Max. Cable Tie Width (metric)</b>	12.7 mm
<b>Mounting Screw Type</b>	#10 (M5) Screw
<b>Width (imperial)</b>	0.76 "
<b>Width (metric)</b>	19.3 mm

