

TECHNICAL DATA SHEET

Part No. PBM10M4
Article No. 151-00231
Type PBM



HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	1000
Carton Qty.	20000
Customs Number	3926909988

For Cable Tie Series	T18 - T50
Height (imperial)	.40 "
Height (metric)	10.20 mm
Length (metric)	10.7 mm
Mounting Hole Diameter (imperial)	0.25 - 0.26 "
Mounting Hole Diameter (metric)	6.25 - 6.55 mm
Panel Thickness (imperial)	0.13 "
Panel Thickness (metric)	3.2 mm
Width (imperial)	0.26 "
Width (metric)	6.6 mm

RoHS ✓

