

TECHNICAL DATA SHEET

Part No. IMP1.7510C2
Article No. 151-00236
Type IMP1.75



Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	White (WH)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Height (imperial)	0.75 "
Height (metric)	19.05 mm
Width (imperial)	1.75 "
Width (metric)	44.45 mm
Width 2 (imperial)	1.28 "
Width 2 (metric)	32.5 mm

