

# TECHNICAL DATA SHEET

**Part No.** IMP2.510M4  
**Article No.** 151-00240  
**Type** IMP2.5



Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Material</b>              | Polyamide 6.6 (PA66)             |
| <b>Operating Temperature</b> | -40°F to +185°F (-40°C to +85°C) |
| <b>Flammability</b>          | UL 94 V-2                        |
| <b>Halogen Free</b>          | Yes                              |
| <b>UV Resistant</b>          | No                               |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use       |
| <b>Color</b>                 | White (WH)                       |
| <b>Pkg. Qty.</b>             | 1000                             |
| <b>Carton Qty.</b>           | 10000                            |
| <b>Customs Number</b>        | 3926909988                       |

|                           |          |
|---------------------------|----------|
| <b>Height (imperial)</b>  | 0.75 "   |
| <b>Height (metric)</b>    | 19.05 mm |
| <b>Width (imperial)</b>   | 2.5 "    |
| <b>Width (metric)</b>     | 63.5 mm  |
| <b>Width 2 (imperial)</b> | 2.03 "   |
| <b>Width 2 (metric)</b>   | 51.56 mm |

