

TECHNICAL DATA SHEET

Part No. MB29M4
Article No. 151-00297
Type MB2



These cable tie mounts are compact in size. They are designed for simple yet robust installation particularly in areas with limited space. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	20000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	0.13 "
Height (metric)	3.30 mm
Length (imperial)	0.81 "
Length (metric)	20.6 mm
Max. Cable Tie Width (imperial)	0.18 "
Max. Cable Tie Width (metric)	4.6 mm
Mounting Hole Diameter (imperial)	0.193 "
Mounting Hole Diameter (metric)	4.9 mm
Mounting Screw Type	#8 (M4) Screw
Width (imperial)	0.49 "
Width (metric)	12.5 mm

