

TECHNICAL DATA SHEET

Part No. MB20M4
Article No. 151-00301
Type MB2



HellermannTyton cable tie screw mounts are used with 18 through 50 pound cable ties to provide stability when securing bundles. The low profile design allows for use in space constrained areas. The mounts are installed quick and easy by securing a single screw.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	20000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	0.13 "
Height (metric)	3.30 mm
Length (imperial)	0.81 "
Length (metric)	20.6 mm
Max. Cable Tie Width (imperial)	0.18 "
Max. Cable Tie Width (metric)	4.6 mm
Mounting Hole Diameter (imperial)	0.193 "
Mounting Hole Diameter (metric)	4.9 mm
Mounting Screw Type	M4 Screw
Width (imperial)	0.49 "
Width (metric)	12.5 mm

HF ✓

RoHS ✓