

TECHNICAL DATA SHEET

Part No. LTM2500C2
Article No. 151-00358
Type LTM250



The lashing tie mount is designed to snap into the T250 lashing tie. The tie head is assembled perpendicular to the mount. The strap is parallel to the mount when inserted into the head. The lashing tie mount is recommended for indoor or outdoor wall mount cable applications.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
For Cable Tie Series	T250
Height (imperial)	0.38 "
Height (metric)	9.6 mm
Length (imperial)	1.5 "
Length (metric)	37.1 mm
Max. Cable Tie Width (imperial)	0.49 "
Max. Cable Tie Width (metric)	12.5 mm
Mounting Screw Type	1/4" (M6) Screw
Width (imperial)	0.73 "
Width (metric)	18.5 mm

