

TECHNICAL DATA SHEET

Part No. 151-00378
Article No. 151-00378
Type IAHC3AH



Automatic Harness Clips offer a simple and secure method of attaching cables to panels and other surfaces. When the cable is pushed inside, it automatically activates the locking features which causes it to close. These are also connectable which allows for multiple cables to be positioned next to each other. These come in various sizes to fit different bundle diameters.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	2.5 "
Height (metric)	64.5 mm
Length (imperial)	1.6 "
Length (metric)	40.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.26 "
Mounting Hole Diameter (metric)	6.2 - 6.7 mm
Panel Thickness (imperial)	0.03 - 0.11 "
Panel Thickness (metric)	0.5-2.7 mm
Width (imperial)	0.4 "
Width (metric)	13.5 mm

RoHS 