

TECHNICAL DATA SHEET

Part No. HDM250HIRC2
Article No. 151-00437
Type HDM25



These mounts contain a small tab inside the mounting hole to temporarily engage the threads, which allows assemblers to preinstall the mount on a stud before securing with a washer and a nut. For use with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	2500
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	0.66 "
Height (metric)	16.7 mm
Length (imperial)	1.41 "
Length (metric)	36.3 mm
Max. Cable Tie Width (imperial)	0.5 "
Max. Cable Tie Width (metric)	12.7 mm
Mounting Screw Type	1/4" (M6) Screw
Width (imperial)	0.75 "
Width (metric)	19.3 mm

