

TECHNICAL DATA SHEET

Part No. 151-00650
Article No. 151-00650
Type SOC8FT6



Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.9 "
Height (metric)	22.5 mm
Length (imperial)	2.2 "
Length (metric)	55.9 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.2 - 6.8 mm
Offset Length (imperial)	0.63 "
Offset Length (metric)	15.9 mm
Panel Thickness (imperial)	0.03 - 0.22 "
Panel Thickness (metric)	0.7 - 5.75 mm
Tape Bar Length (imperial)	2.40 "
Tape Bar Length (metric)	61.0 mm
Width (imperial)	0.35 "
Width (metric)	9.0 mm

