

TECHNICAL DATA SHEET

Part No. 151-00651
Article No. 151-00651
Type TC6FT6LG



HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	1.0 "
Height (metric)	26.60 mm
Length (imperial)	1.5 "
Length (metric)	38.1 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.2 - 6.8 mm
Panel Thickness (imperial)	0.03 - 0.71 "
Panel Thickness (metric)	0.7 - 18.0 mm
Tape Bar Length (imperial)	1.55 "
Tape Bar Length (metric)	39.3 mm
Width (imperial)	0.5 "
Width (metric)	12.0 mm

HF ✓

RoHS ✓