

# TECHNICAL DATA SHEET

**Part No.** 151-00663  
**Article No.** 151-00663  
**Type** TC6FT6



HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Operating Temperature, 500h</b>	+329°F (+165°C)
<b>Operating Temperature, 1000h</b>	+320°F (+160°C)
<b>Operating Temperature, 5000h</b>	+257°F (+125°C)
<b>Flammability</b>	UL 94 HB
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	10000
<b>Carton Qty.</b>	10000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree
<b>Height (imperial)</b>	.50 "
<b>Height (metric)</b>	14.0 mm
<b>Length (imperial)</b>	1.5 "
<b>Length (metric)</b>	38.1 mm
<b>Mounting Hole Diameter (imperial)</b>	0.24 - 0.27 "
<b>Mounting Hole Diameter (metric)</b>	6.2 - 6.8 mm
<b>Panel Thickness (imperial)</b>	0.03 - 0.71 "
<b>Panel Thickness (metric)</b>	0.7 - 5.75 mm
<b>Tape Bar Length (imperial)</b>	1.55 "
<b>Tape Bar Length (metric)</b>	39.3 mm
<b>Width (imperial)</b>	0.5 "
<b>Width (metric)</b>	12.0 mm

RoHS 