

TECHNICAL DATA SHEET

Part No. 151-00667
Article No. 151-00667
Type WAC075



The WAC Adhesive cable clamps are designed with lead in angles allowing for easy insertion of wires and cables. The rubber based adhesive allows for a permanent bond to most surfaces. Available in two sizes.

Material	Polyvinylchloride (PVC)
Adhesive	Self adhesive
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	0.62 "
Height (metric)	15.8 mm
Height 2 (imperial)	1.05 "
Height 2 (metric)	26.7 mm
Length (imperial)	1.13 "
Length (metric)	28.7 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.1 mm
Min. Bundle Diameter (imperial)	0.5 "
Min. Bundle Diameter (metric)	12.7 mm
Width (imperial)	1.0 "
Width (metric)	25.4 mm