

TECHNICAL DATA SHEET

Part No. 151-00669
Article No. 151-00669
Type WAC100



The WAC Adhesive cable clamps are designed with lead in angles allowing for easy insertion of wires and cables. The rubber based adhesive allows for a permanent bond to most surfaces. Available in two sizes.

Material	Polyvinylchloride (PVC)
Adhesive	Self adhesive
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	100
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	0.85 "
Height (metric)	21.6 mm
Height 2 (imperial)	1.35 "
Height 2 (metric)	34.3 mm
Length (imperial)	1.5 "
Length (metric)	38.1 mm
Max. Bundle Diameter (imperial)	1 "
Max. Bundle Diameter (metric)	25.4 mm
Min. Bundle Diameter (imperial)	0.75 "
Min. Bundle Diameter (metric)	19.1 mm
Width (imperial)	1.25 "
Width (metric)	31.8 mm