

TECHNICAL DATA SHEET

Part No. 151-00677
Article No. 151-00677
Type CC08



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	5000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	0.99 "
Length (metric)	25.2 mm
Mounting Hole Diameter (imperial)	0.25 - 0.27 "
Mounting Hole Diameter (metric)	6.25 - 6.75 mm
Panel Thickness (imperial)	0.03 - 0.23 "
Panel Thickness (metric)	0.7 - 5.75 mm
Width (imperial)	0.78 "
Width (metric)	19.81 mm

