

TECHNICAL DATA SHEET

Part No. 151-00757
Article No. 151-00757
Type CTAM1



Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.

Material	Polyetheretherketone (PEEK)
Operating Temperature	-67°F to +464°F (-55°C to +240°C)
Flammability	UL 94 V-0
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Beige (BGE)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	0.22 "
Height (metric)	5.5 mm
Length (imperial)	0.81 "
Length (metric)	20.5 mm
Max. Cable Tie Width (imperial)	0.2 "
Max. Cable Tie Width (metric)	5.0 mm
Mounting Hole Diameter (imperial)	0.17 "
Mounting Hole Diameter (metric)	4.3 mm
Mounting Screw Type	M4 Screw
Width (imperial)	0.4 "
Width (metric)	10.2 mm

RoHS 