

TECHNICAL DATA SHEET

Part No. 151-00765
Article No. 151-00765
Type CC09



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated to a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Length (imperial)	1.30 "
Length (metric)	33.05 mm
Mounting Hole Diameter (imperial)	0.35 x 0.67 "
Mounting Hole Diameter (metric)	9.0 x 17.0 mm
Panel Thickness (imperial)	0.02 - 0.25 "
Panel Thickness (metric)	0.6 - 6.4 mm
Width (imperial)	0.85 "
Width (metric)	21.59 mm

