

# TECHNICAL DATA SHEET

**Part No.** 151-00783  
**Article No.** 151-00783  
**Type** CTCFT6



Convoluted Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                |
| <b>UV Resistant</b>          | No                                                               |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                       |
| <b>Color</b>                 | Black (BK)                                                       |
| <b>Pkg. Qty.</b>             | 5003                                                             |
| <b>Carton Qty.</b>           | 5000                                                             |
| <b>Customs Number</b>        | 3926909988                                                       |

|                                          |               |
|------------------------------------------|---------------|
| <b>Height (imperial)</b>                 | 0.73 "        |
| <b>Height (metric)</b>                   | 18.5 mm       |
| <b>Max. Bundle Diameter (imperial)</b>   | 0.59 "        |
| <b>Max. Bundle Diameter (metric)</b>     | 15.0 mm       |
| <b>Min. Bundle Diameter (imperial)</b>   | 0.43 "        |
| <b>Min. Bundle Diameter (metric)</b>     | 11.0 mm       |
| <b>Mounting Hole Diameter (imperial)</b> | 0.25 - 0.26 " |
| <b>Mounting Hole Diameter (metric)</b>   | 6.3 - 6.7 mm  |
| <b>Panel Thickness (imperial)</b>        | 0.03 - 0.18 " |
| <b>Panel Thickness (metric)</b>          | 0.7 - 4.5 mm  |
| <b>Width (imperial)</b>                  | 0.43 "        |
| <b>Width (metric)</b>                    | 11.0 mm       |

RoHS 