

TECHNICAL DATA SHEET

Part No. 151-00812
Article No. 151-00812
Type HM5



HellermannTyton H-Mounts offer a secure bundling solution that utilizes existing frame rail bolts which reduces component costs and improves installation time. The H-mounts have three bundle mounting locations each accommodating ties up to 1/2" wide. H-Mounts fasten with three bolt sizes: 1/2", 5/8", and 3/4". The top tie slot allows the bundle to be positioned directly over the bolt. The two curved tie slots on the sides position the bundles adjacent to the bolt yet away from the frame.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	900
Carton Qty.	900
Customs Number	3926909988

Height (imperial)	1.10 "
Height (metric)	28.0 mm
Length (imperial)	1.97 "
Length (metric)	50.0 mm
Stud Diameter (imperial)	0.50 "
Width (imperial)	1.02 "
Width (metric)	25.98 mm

