

TECHNICAL DATA SHEET

Part No. 151-00834
Article No. 151-00834
Type YCCKSFT62x122PT1.7-2.3 90°



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10000
Carton Qty.	10000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Length (metric)	27.0 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm
Panel Thickness (imperial)	0.07 - 0.09 "
Panel Thickness (metric)	1.7 - 2.3 mm
Width (metric)	21.0 mm

