

TECHNICAL DATA SHEET

Part No. 151-00838
Article No. 151-00838
Type SSPC5



Stainless steel P-mounts provide a robust and extremely durable mounting solution for a wide range of applications. With a 10 mm slot width and either a 4 mm, 5 mm or 6 mm fastener hole, this two-way mount can be installed quickly and easily with a single screw or bolt, providing excellent performance and a high pull force. Designed for use with MBTS(-S), MBTH(-S) and MBTSFC stainless steel ties, or 18 through 120 pound nylon cable ties to provide stability when securing bundles.

Material	Stainless Steel (SS316L)
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Flammability	Non-burning
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Metal (ML)
Pkg. Qty.	100
Carton Qty.	2000
Customs Number	7326908695

Fixation Method	Screw Mounting and Rivet
Height (imperial)	0.18 "
Height (metric)	4.5 mm
Length (imperial)	0.91 "
Length (metric)	23.0 mm
Max. Cable Tie Width (imperial)	0.39 "
Max. Cable Tie Width (metric)	10.0 mm
Mounting Hole Diameter (metric)	5.3 mm
Mounting Screw Type	M5 Screw
Width (imperial)	0.40 "
Width (metric)	10.2 mm

HF ✓

LFH ✓

RoHS ✓