

TECHNICAL DATA SHEET

Part No. 151-00903
Article No. 151-00903
Type SOC10FT6LG



Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.60 "
Height (metric)	14.50 mm
Length (imperial)	2.3 "
Length (metric)	58.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 ", 0.24 - 0.26 " (HEXAGONAL)
Mounting Hole Diameter (metric)	6.1 - 6.6 mm
Offset Length (imperial)	1.71 "
Offset Length (metric)	43.35 mm
Panel Thickness (imperial)	0.02 - 0.23 "
Panel Thickness (metric)	0.6 - 5.75 mm
Tape Bar Length (metric)	58.0 mm
Width (imperial)	0.6 "
Width (metric)	16.0 mm

