

TECHNICAL DATA SHEET

Part No. 151-00927
Article No. 151-00927
Type SC6.6



The C Clip with fir tree mount is ideal for panels with pre-drilled holes. Easy installation by hand eliminates the need for any tools. Once installed, the cable simply snaps into the clip. The cable can be removed and reinstalled without removing the clip. Made from PA66HIRHSUV material, the clip offers increased flexibility along with heat resistance and UV stability.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	1.32 "
Height (metric)	33.43 mm
Mounting Hole Diameter (imperial)	0.26 "
Mounting Hole Diameter (metric)	6.6 mm
Panel Thickness (imperial)	0.03 - 0.25 "
Panel Thickness (metric)	0.7 - 6.35 mm
Width (imperial)	0.72 "
Width (metric)	18.26 mm

