

TECHNICAL DATA SHEET

Part No. 151-00993
Article No. 151-00993
Type BC90FT6



HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner and fixated into the panel at this location.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	1.03 "
Height (metric)	26.2 mm
Length (imperial)	0.98 "
Length (metric)	25.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.1 - 6.9 mm
Panel Thickness (imperial)	0.02 - 0.24 "
Panel Thickness (metric)	0.7 - 6.0 mm
Tape Bar Length (metric)	50.0 mm
Width (imperial)	0.06 "
Width (metric)	1.5 mm

RoHS 