

TECHNICAL DATA SHEET

Part No. 151-01022
Article No. 151-01022
Type LOC15-19FT6LG



The Locking Omega Clamp fully encircles and securely locks around wire bundles ranging from 15-19 mm. Its uniquely engineered fir tree holds tightly in hole sizes from 6.1 mm to 7 mm. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Depth (imperial)	0.47 "
Depth (metric)	12.0 mm
Height (imperial)	1.87 "
Height (metric)	47.5 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.0 mm
Min. Bundle Diameter (imperial)	0.59 "
Min. Bundle Diameter (metric)	15.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.26 " (HEXAGONAL), 0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 6.6 mm (hexagonal), 6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.32 "
Panel Thickness (metric)	0.6 - 8.25 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

