

TECHNICAL DATA SHEET

Part No. 151-01023
Article No. 151-01023
Type LOC15-19FT6LG2



The Locking Omega Clip creates a full and secure lock completely around a wire bundle ranging from 5-25 mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by utilizing a round or oval hole.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	2.57 "
Height (metric)	65.27 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.0 mm
Min. Bundle Diameter (imperial)	0.59 "
Min. Bundle Diameter (metric)	15.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.26 " (HEXAGONAL), 0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 6.6 mm (hexagonal), 6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.32 "
Panel Thickness (metric)	0.6 - 8.25 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

RoHS 