

# TECHNICAL DATA SHEET

**Part No.** 151-01033  
**Article No.** 151-01033  
**Type** CCOVAL6



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

|                                     |                                                                          |
|-------------------------------------|--------------------------------------------------------------------------|
| <b>Material</b>                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Operating Temperature</b>        | -40°F to +221°F (-40°C to +105°C)                                        |
| <b>Operating Temperature, 500h</b>  | +329°F (+165°C)                                                          |
| <b>Operating Temperature, 1000h</b> | +320°F (+160°C)                                                          |
| <b>Operating Temperature, 5000h</b> | +257°F (+125°C)                                                          |
| <b>Flammability</b>                 | UL 94 HB                                                                 |
| <b>Halogen Free</b>                 | Yes                                                                      |
| <b>UV Resistant</b>                 | Yes                                                                      |
| <b>Use Conditions</b>               | For Indoor and Outdoor Use                                               |
| <b>Color</b>                        | Black (BK)                                                               |
| <b>Pkg. Qty.</b>                    | 1000                                                                     |
| <b>Carton Qty.</b>                  | 4000                                                                     |
| <b>Customs Number</b>               | 3926909988                                                               |

|                                          |                                                            |
|------------------------------------------|------------------------------------------------------------|
| <b>Fixation Method</b>                   | Fir Tree for oval holes                                    |
| <b>Length (imperial)</b>                 | 1.16 "                                                     |
| <b>Length (metric)</b>                   | 29.34 mm                                                   |
| <b>Mounting Hole Diameter (imperial)</b> | 0.24 x 0.48 ", 0.26 x 0.50 ", 0.26 x 0.51 ", 0.28 x 0.47 " |
| <b>Mounting Hole Diameter (metric)</b>   | 6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm |
| <b>Panel Thickness (imperial)</b>        | 0.02 - 0.12 "                                              |
| <b>Panel Thickness (metric)</b>          | 0.6 - 3.0 mm                                               |
| <b>Width (imperial)</b>                  | 0.69 "                                                     |
| <b>Width (metric)</b>                    | 17.6 mm                                                    |

