

TECHNICAL DATA SHEET

Part No. 151-01049
Article No. 151-01049
Type LOC15-19FTOVAL



The Locking Clamp is ideal for fastening wire and cable bundles to panels. Its uniquely engineered fir tree holds tightly in pre-stamped hole sizes. The locking clamp mechanism dynamically fits various bundle sizes, while an integrated cable tie saddle allows installers to add additional cable runs. The clamp is manufactured of an impact-modified Polyamide 6.6 material for increased flexibility, heat resistance and UV stabilization to deliver years of dependable performance. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs. Fits five common, pre-stamped hole sizes: 6.2x12.2 mm, 6.5x12.5 mm, 6.5x13 mm, 7x12 mm and 9x14 mm.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Depth (imperial)	0.47 "
Depth (metric)	12.0 mm
Height (imperial)	1.95 "
Height (metric)	49.5 mm
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.0 mm
Min. Bundle Diameter (imperial)	0.59 "
Min. Bundle Diameter (metric)	15.0 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.26 x 0.49 ", 0.26 x 0.51 ", 0.28 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

