

TECHNICAL DATA SHEET

Part No. 151-01109
Article No. 151-01109
Type BC90AH2



HellermannTyton's Bundling Clips create a solution that allows the harness to be routed around a corner, and fixated into the panel at this location.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.93 "
Height (metric)	23.6 mm
Length (imperial)	0.98 "
Length (metric)	25.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.27 "
Mounting Hole Diameter (metric)	6.2 - 6.8 mm
Panel Thickness (imperial)	0.04 - 0.06 "
Panel Thickness (metric)	1.0 - 1.5 mm
Tape Bar Length (metric)	50.0 mm
Width (imperial)	0.06 "
Width (metric)	1.5 mm

RoHS