

TECHNICAL DATA SHEET

Part No. 151-01144
Article No. 151-01144
Type CC11



Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Length (imperial)	1.18 "
Length (metric)	30.0 mm
Mounting Hole Diameter (imperial)	0.35 x 0.63 ", 0.35 x 0.67 "
Mounting Hole Diameter (metric)	9.0 x 16.0 mm, 9.0 x 17.0 mm
Panel Thickness (imperial)	0.02 - 0.26 "
Panel Thickness (metric)	0.6 - 6.5 mm
Width (imperial)	0.72 "
Width (metric)	18.2 mm

