

TECHNICAL DATA SHEET

Part No. 151-01238
Article No. 151-01238
Type SOC12FTOVAL



Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)

Pkg. Qty.	1500
Carton Qty.	1500
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Height (imperial)	0.79 "
Height (metric)	20.0 mm
Length (imperial)	1.97 "
Length (metric)	50.0 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.25 x 0.50 ", 0.27 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Offset Length (imperial)	1.26 "
Offset Length (metric)	32.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Tape Bar Length (imperial)	1.97 "
Tape Bar Length (metric)	50.0 mm
Width (imperial)	0.37 "
Width (metric)	9.5 mm

