

# TECHNICAL DATA SHEET

**Part No.** 151-01239  
**Article No.** 151-01239  
**Type** BCFTOVAL



HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

<b>Material</b>	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Operating Temperature, 500h</b>	+329°F (+165°C)
<b>Operating Temperature, 1000h</b>	+320°F (+160°C)
<b>Operating Temperature, 5000h</b>	+257°F (+125°C)
<b>Flammability</b>	UL 94 HB
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Natural (NA)
<b>Pkg. Qty.</b>	8000
<b>Carton Qty.</b>	8000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree for oval holes
<b>Height (imperial)</b>	0.60 "
<b>Height (metric)</b>	15.45 mm
<b>Length (imperial)</b>	2.28 "
<b>Length (metric)</b>	58.0 mm
<b>Mounting Hole Diameter (imperial)</b>	0.24 x 0.48 ", 0.25 x 0.50 ", 0.27 x 0.47 "
<b>Mounting Hole Diameter (metric)</b>	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
<b>Panel Thickness (imperial)</b>	0.02 - 0.24 "
<b>Panel Thickness (metric)</b>	0.6 - 6.0 mm
<b>Tape Bar Length (imperial)</b>	2.28 "
<b>Tape Bar Length (metric)</b>	58.0 mm
<b>Width (imperial)</b>	0.5 "
<b>Width (metric)</b>	12.0 mm

