

# TECHNICAL DATA SHEET

**Part No.** 151-01296  
**Article No.** 151-01296  
**Type** CC18



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Operating Temperature, 500h</b>	+329°F (+165°C)
<b>Operating Temperature, 1000h</b>	+320°F (+160°C)
<b>Operating Temperature, 5000h</b>	+257°F (+125°C)
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	3000
<b>Carton Qty.</b>	3000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Fir Tree for oval holes
<b>Length (imperial)</b>	1.19 "
<b>Length (metric)</b>	30.29 mm
<b>Mounting Hole Diameter (imperial)</b>	0.35 x 0.67 "
<b>Mounting Hole Diameter (metric)</b>	9.0 x 17.0 mm
<b>Panel Thickness (imperial)</b>	0.02 - 0.37 "
<b>Panel Thickness (metric)</b>	0.6 - 9.5 mm
<b>Width (imperial)</b>	0.80 "
<b>Width (metric)</b>	20.32 mm