

TECHNICAL DATA SHEET

Part No. 151-01311
Article No. 151-01311
Type TC900VAL



HellermannTyton's bundling clips allow a harness to be routed around a corner and attached to the panel at this location.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Bolt
Height (imperial)	1.66 "
Height (metric)	40.8 mm
Length (imperial)	1.47 "
Length (metric)	37.3 mm
Mounting Hole Diameter (imperial)	0.27 x 0.51 "
Mounting Hole Diameter (metric)	6.5 x 12.5 mm
Tape Bar Length (imperial)	1.60 "
Tape Bar Length (metric)	40.8 mm
Width (imperial)	0.59 "
Width (metric)	15.0 mm

