

TECHNICAL DATA SHEET

Part No. 151-01403
Article No. 151-01403
Type BCFTOVAL



HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	8000
Carton Qty.	8000
Customs Number	3926909988

Fixation Method	Fir Tree for oval holes
Height (imperial)	0.60 "
Height (metric)	15.45 mm
Length (imperial)	2.28 "
Length (metric)	58.0 mm
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.25 x 0.50 ", 0.27 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.24 "
Panel Thickness (metric)	0.5 - 6.0 mm
Tape Bar Length (imperial)	2.28 "
Tape Bar Length (metric)	58.0 mm

RoHS 